



PRODUCT DATA SHEET

Sanitary cleaning - Maintenance cleaners

Wetrok Reocid

Gentle scented sanitary cleaner - prevents limescale build-up where water hardness is low to moderate





Wetrok Reocid



pH value (Concentrate): 4.5–5.5

Important ingredients:

Surfactants, Solvents, Acid, Fragrances, Preservatives, Colourant

Recommended dosage:



Maintenance cleaning

0.1–0.2 l/10 l



Intermediate cleaning

0.4–0.5 l/10 l



Foaming by hand (foam bottle)

2 l/10 l

**METHODS
finder**



APPLICATION

- The gentle sanitary cleaner with a strong scent
- For maintenance cleaning of washable and acid-resistant surfaces and equipment (sanitary porcelain, fittings, ceramic tiles, bathrooms, showers, washrooms and WCs, etc.)

PROPERTIES

- High-lather
- Slightly acidic
- Heavily scented
- Reduces the build-up of limescale when used regularly
- Leaves a long-lasting scent

GOOD TO KNOW

- The exterior of sanitary fittings must not be warm when cleaning
- Alternating between different deodorizing cleaners will increase the facility users' awareness of the scent and therefore promote a sense of cleanliness

PLEASE NOTE

- Not suitable for acid-sensitive surfaces (limestone, marble, clinker, aluminium, etc.)

RECOMMENDED APPLICATION METHOD

Damp wiping (manual foaming)

Apply the cleaning foam in an "X" form on a folded cloth, then damp wipe the surface (use the fold technique). Rinse the cleaned surface with clean, cold water and wipe it dry as needed.

Wet wiping (by hand)

Wash the dirty surface with cleaning solution. Wet scrub using a suitable hand pad or brush. Use a cloth to remove the dissolved dirt and the remaining cleaning solution. Rinse the cleaned surface with clean, cold water and wipe it dry as needed.

STORAGE

Store in original container at 15 to 25°C and protected from sunlight. Keep container closed when not in use.

Durability (unopened): 24 Month

Wetrok AG shall have no liability whatsoever for damage caused by incorrect use. Observe special cleaning and care instructions from the floor covering manufacturer.